

PMB Moisture Analyzer

Streamlines moisture analysis for fast and accurate results

With rapid response time and easy-to-use functionality, Adam Equipment's PMB moisture analyzers set a new standard for data communication, making recording results quick and effortless. The USB interface means you can connect a flash drive to download results in real time and store them for future analysis. Self-contained software allows you to take readings directly from the balance, giving users freedom to collect data on a production floor or in the field. The automatic test-setting function lets you swiftly run multiple tests without additional user input, and the built-in memories enables you to store that data for later reference.

Applications

- Weighing
- Moisture determination

Features

- Programmable backlight can be set to "always on", "always off" or "light only when weighing"
- RS-232 interface for connection to computers and printers
- USB host for memory card and USB I/O interface
- Three settings for heating sample include ramp-up, stepped temperatures and single temperature
- Seven preset drying modes allow test routines for several products
- Allows automatic test start upon lid closure
- Built-in memory for storing products and settings
- Temperature setting to from 50-160°C in 1°C increments



| Model | PMB 53 | PMB 202 |
|-----------------------|--|---------------|
| Capacity | 50g | 200g |
| Readability | 0.001g / 0.01% | 0.01g / 0.05% |
| Tare Range | | Full range |
| Pan Size | | 100mm ø |
| Weighting Units | g, %M, %S, ATRO %M, ATRO %S | |
| Calibration | External calibration | |
| Display | Backlit LCD with 24mm-high digits | |
| Memory Settings | Internal memory stores up to 99 test results and 49 programmable user settings External USB drive for limitless data storage of test results and settings | |
| Power Supply | Mains power cord | |
| Operating Temperature | 0° to 40°C | |
| Overall Dim. | 250x360x185mm | |



www.adamequipment.com

©2013 Adam Equipment